



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2176093-5
RP 2A 0.25W 10K 0.1% 25PPM 1K RL




TE Part # 1-2176092-8
RP 2A 0.25W 1K0 0.1% 25PPM 1K RL



TE Part # 2176308-5
RP 1E 0.1W 147K 0.1% 25PPM 5K RL




TE Part # 1625867-2
RP 1J 0.166W 10K 0.1% 25PPM 1K RL



TE Part # 2-2176308-7
RP 1E 0.1W 249K 0.1% 25PPM 5K RL

Also in the Series | [Holsworthy RP73](#)



[Surface Mount Resistors\(4227\)](#)

Customers Also Bought



TE Part #1658614-2
25 POS HDF RCPT, AP, LEAD FREE



TE Part #1757820-7
AMPLIMITE,ASY,RCPT,STD,109,ZN,2, CT




TE Part #1614349-9
RN 0603 10K 0.1% 10PPM CUT LENGTH



TE Part #2177059-1
PROTECTION CAP,180DEG



TE Part #1757823-8
AMPLIMITE,ASY,PLUG,STD,90,ZN,2,CT



TE Part #1-826629-6
16X1 AMPMODU II HDR ST



TE Part #1757819-6
AMPLIMITE,ASY,PLUG,STD,109,ZN,1, CT



TE Part #1-2177053-2
2POS,8MM HV,PLUG HSG,ASSY, SEALED



TE Part #621065-000
[D-142-65](#)



TE Part #1337772-1
[50/OHM COAX BNC STR PLUG-ELB P](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-2176087-7_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-2176087-7_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-2176087-7_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RP73-0915](#)

English