



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-2308272-3
CABLE CLAMP3 (CASE RAW)



TE Part #3-1879208-7
CPF 0402 330R 0.1% 25PPM 1K RL



TE Part #4-1879208-7
CPF 0402 820R 0.1% 25PPM 1K RL



TE Part #1-1879126-9
RN 0402 130R 0.1% 10PPM CUT LENGTH





TE Part #539663-2

MATRIZE MICRO T.EDS



TE Part #1-1393565-8

C42334A 100C 51=RP PASS-STIFT



TE Part #2-1393565-1

C42334A 100C 56=RP PASS-BUCHSE

TE Part #2-1393586-1

V23535A2200A340=BKMOD421
HEADE

TE Part #1393725-1

C42334A 40A 6=RP622 FEDERLEI

TE Part #4-1393565-4

C42334A 228C175=RP RIEGELWANNE