

LEITERPLATTENADAPTER FUER Han



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 000 9905
Specification	LEITERPLATTENADAPTER FUER Han
HARTING eCatalogue	https://harting.com/09120009905

Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	5 poles In the Han® Q 5/0

Version

Gender	Male Female
Details	for PCB's up to 2.4 mm

Technical characteristics

Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

Material properties

Material (insert)	Polycarbonate (PC)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	10
Net weight	3.94 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140016309
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)