





REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1、Rated voltage: 250V AC.DC.
 - 2、Rated current: 3A AC.DC.
 - 3、Contact resistance: ≤20 mΩ.
 - 4、Insulation resistance: ≥1000 MΩ.
 - 5、Withstand voltage : 1000V AC/minute.
 - 6、Ambient temperature: -40℃~+105℃.
 - 7、Materials: Nylon UL94V-0(2).
 - 8、Pin Material: Brass.Tin-Plated.
 - 9、Green Material RoHS Compliant.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
02	250-2A	2.5	5.0	09	250-9A	20.0	22.5
03	250-3A	5.0	7.5	10	250-10A	22.5	25.0
04	250-4A	7.5	10.0	11	250-11A	25.0	27.5
05	250-5A	10.0	12.5	12	250-12A	27.5	30.0
06	250-6A	12.5	15.0	13	250-13A	30.0	32.5
07	250-7A	15.0	17.5	14	250-14A	32.5	35.0
08	250-8A	17.5	20.0	15	250-15A	35.0	37.5

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25014 (250)-A	TITLE: 2.50 mm Pitch Wire To Board Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Yuan Jun rong	DATE:21/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21/08/01
FINISH:		APPD:Ren An De	DATE:21/08/01
DRAWING NO:			
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1、Rated voltage: 250V AC.DC.
 - 2、Rated current: 3A AC.DC.
 - 3、Contact resistance: $\leq 20\text{ m}\Omega$.
 - 4、Insulation resistance: $\geq 1000\text{ M}\Omega$.
 - 5、Withstand voltage : 1000V AC/minute.
 - 6、Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$.
 - 7、Materials: Nylon UL94V-0(2).
 - 8、Pin Material: Brass.Tin-Plated.
 - 9、Green Material RoHS Compliant.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
02	250-2AW	2.5	5.0	09	250-9AW	20.0	22.5
03	250-3AW	5.0	7.5	10	250-10AW	22.5	25.0
04	250-4AW	7.5	10.0	11	250-11AW	25.0	27.5
05	250-5AW	10.0	12.5	12	250-12AW	27.5	30.0
06	250-6AW	12.5	15.0	13	250-13AW	30.0	32.5
07	250-7AW	15.0	17.5	14	250-14AW	32.5	35.0
08	250-8AW	17.5	20.0	15	250-15AW	35.0	37.5

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL25014 (250)-AW	TITLE: 2.50 mm Pitch Wire To Board Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR: Yuan Jun rong	DATE:21/08/01
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:21/08/01
FINISH:		APPD:Ren An De	DATE:21/08/01
DRAWING NO:			




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1、Rated voltage: 250V AC.DC.
 - 2、Rated current: 3A AC.DC.
 - 3、Contact resistance: $\leq 20\text{ m}\Omega$.
 - 4、Insulation resistance: $\geq 1000\text{ M}\Omega$.
 - 5、Withstand voltage : 1000V AC/minute.
 - 6、Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$.
 - 7、Materials: Nylon UL94V-0(2).
 - 8、Pin Material: Brass.Tin-Plated.
 - 9、Green Material RoHS Compliant.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
02	250-2AWT	2.5	5.0	09	250-9AWT	20.0	22.5
03	250-3AWT	5.0	7.5	10	250-10AWT	22.5	25.0
04	250-4AWT	7.5	10.0	11	250-11AWT	25.0	27.5
05	250-5AWT	10.0	12.5	12	250-12AWT	27.5	30.0
06	250-6AWT	12.5	15.0	13	250-13AWT	30.0	32.5
07	250-7AWT	15.0	17.5	14	250-14AWT	32.5	35.0
08	250-8AWT	17.5	20.0	15	250-15AWT	35.0	37.5

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL25014 (250)-AWT	TITLE: 2.50 mm Pitch Wire To Board Housing
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Yuan Jun rong	DATE:21/08/01
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:21/08/01
FINISH:		APPD:Ren An De	DATE:21/08/01
DRAWING NO: GC-DL25014-XXWT-XXX-XX-X-XX			




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1、Rated voltage: 250V AC.DC.
 - 2、Rated current: 3A AC.DC.
 - 3、Contact resistance: ≤20 mΩ.
 - 4、Insulation resistance: ≥1000 MΩ.
 - 5、Withstand voltage : 1000V AC/minute.
 - 6、Ambient temperature: -40℃~+105℃.
 - 7、Materials: Nylon UL94V-0(2).
 - 8、Green Material RoHS Compliant.


Circ uits	Product name	Dimension mm			Circ uits	Product name	Dimension mm		
		A	B	C			A	B	C
2	250-2Y	2.5	7.0	6.0	9	250-9Y	20.0	24.5	23.5
3	250-3Y	5.0	9.5	8.5	10	250-10Y	22.5	27.0	26.0
4	250-4Y	7.5	12.0	11.0	11	250-11Y	25.0	29.5	28.5
5	250-5Y	10.0	14.5	13.5	12	250-12Y	27.5	32.0	31.0
6	250-6Y	12.5	17.0	16.0	13	250-13Y	30.0	34.5	33.5
7	250-7Y	15.0	19.5	18.5	14	250-14Y	32.5	37.0	36.0
8	250-8Y	17.5	22.0	21.0	15	250-15Y	35.0	39.5	38.5


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25014 (250)-Y		TITLE: 2.50 mm Pitch Wire To Board Housing	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Yuan Jun rong	DATE:21/08/01	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:21/08/01		
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV. : A

REV.	REVISION DESCRIPTION	DATE	APPD



- NOTES:
- 1、Rated voltage: 250V AC.DC.
 - 2、Rated current: 3A AC.DC.
 - 3、Contact resistance: $\leq 20\text{ m}\Omega$.
 - 4、Insulation resistance: $\geq 1000\text{ M}\Omega$.
 - 5、Withstand voltage : 1000V AC/minute.
 - 6、Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$.
 - 7、Materials: Phosphor bronze; Tin-plated.
 - 8、Green Material RoHS Compliant.



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25014 (250)-T		TITLE: 2.50 mm Pitch Wire To Board Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Yuan Jun rong	DATE:21.11.27	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:21.11.27		
DRAWING NO:		APPD:Ren An De	DATE:21.11.27	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV.: A