


PXP6010/02S/ST/0405 Datasheet

Product Name // Flex Cable Connector PXP6010 Series 2
Contact Socket Screw Termination (contacts supplied fitted) 4mm-5mm Cable (Dark Grey Gland) Plastic Body

 [View Product Page](#)



// Product Description:

- Flex Cable Connectors
 - Water and dustproof to IP66, IP68, IP69K when mated with compatible connector
 - 30 degree push twist locking, tamperproof lock prevents accidental un-mating
 - Socket
 - 2 Contacts
 - Screw contacts supplied fitted
- Plastic Body
 - Cable acceptance 4mm-5mm diameter
 - Gland Pack PXP6088 available separately to accomodate all sizes
 - PXP6081 Sealing Cap available separately to maintain IP rating of unmated connectors
 - Mate with PXP6011 Series Inline, PXP6012 and PXP6014 Series Front Panel Mount Connectors

// General Information:

Product Display Title:	Flex Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	6000 Series Buccaneer
Approvals:	UL
Body Colour:	Grey
Body Material:	Polycarbonate/Polybutylene Terephthalate (PC/PBT)
Body Material Type:	Plastic Body
Contact Type:	Socket Contact
Coupling Type:	Push-Twist
Current Max:	16A, 11A
Diameter Over Coupling Ring Mm:	32mm
Flamability Rating:	UL94V-0
Function:	Flex Cable Connector
Insulation Resistance:	>10 ⁶ MΩ @500V DC
Ip Rating:	IP66, IP68, IP69K
Max Cable Entry Size:	5mm
Min Cable Entry Size:	4mm
Max Contact Accomodation Awg:	14AWG
Min Contact Accomodation Awg:	14AWG
Max Contact Accomodation Mm2:	2.5mm2
Min Contact Accomodation Mm2:	2.5mm2
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	2 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1
Voltage Max:	277V

// Product PDF Links

-  6000 Series power connectors...
-  6000 Series metal body power...

// Product 3D CAD Model Links

-  PXP6010/02S/ST/04053D CAD Model



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)