

RP73PG1J470RFTD


✕ OBSOLETE

Holsworthy | Holsworthy RP73

TE Internal #: 4-2176090-1

TE Internal Description: RP 1J 0.166W 470R 1% 50PPM 5K RL

[View on TE.com >](#)



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Holsworthy RP73](#)




Surface Mount Resistors(4227)

Customers Also Bought



TE Part #9-1625971-5  
HSA25 R01 10%



TE Part #2337238-3  
TACT MINI GW 5.2X5.2X2 160GF



TE Part #3-2176307-2  
RP 1E 0.1W 26K1 0.1% 25PPM 5K RL




TE Part #7-2176305-3  
RP 1E 0.1W 604R 0.1% 25PPM 5K RL



TE Part #1-1879353-9  
RR02 5% 24K AMMO




TE Part #7-1879354-5  
RR03 5% 390R AMMO




TE Part #7-1879648-1  
H4P 287R 0.5% 100PPM



TE Part #1-830611-0  
LGH 1/2 SNGL MLD END



TE Part #3-1437162-8  
FSP-12A-11



TE Part #2-2176392-9  
RQ 1206 261K 0.1% 10PPM 5K RL

Documents

Product Drawings

RP 1J 0.166W 470R 1% 50PPM 5K RL

English

Datasheets & Catalog Pages

RP73-0915

English