

# D-UKK 3-MSTB-5,08 - End cover

2770891

<https://www.phoenixcontact.com/us/products/2770891>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End cover, pitch: 5.08 mm, depth: 53.5 mm, width: 2.5 mm, height: 50 mm, number of positions: 1, color: gray

## Commercial data

|                                      |                    |
|--------------------------------------|--------------------|
| Item number                          | 2770891            |
| Packing unit                         | 50 pc              |
| Minimum order quantity               | 50 pc              |
| Sales key                            | BE19               |
| Product key                          | BE1Z1X             |
| Catalog page                         | Page 324 (CL-2005) |
| GTIN                                 | 4017918068127      |
| Weight per piece (including packing) | 4.01 g             |
| Weight per piece (excluding packing) | 3.91 g             |
| Customs tariff number                | 85389099           |
| Country of origin                    | DE                 |

# D-UKK 3-MSTB-5,08 - End cover

2770891

<https://www.phoenixcontact.com/us/products/2770891>



## Technical data

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | End cover        |
| Product family      | DECKEL + RZ + DP |
| Number of positions | 1                |
| Pitch               | 5.08 mm          |

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

### Material specifications

|                                        |                 |
|----------------------------------------|-----------------|
| Color                                  | gray (RAL 7042) |
| Material                               | PA              |
| Flammability rating according to UL 94 | V0              |

### Dimensions

|        |         |
|--------|---------|
| Width  | 2.5 mm  |
| Height | 50 mm   |
| Depth  | 53.5 mm |
| Pitch  | 5.08 mm |

# D-UKK 3-MSTB-5,08 - End cover



2770891

<https://www.phoenixcontact.com/us/products/2770891>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27141133 |
| ECLASS-12.0 | 27141133 |
| ECLASS-13.0 | 27250301 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000886 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# D-UKK 3-MSTB-5,08 - End cover



2770891

<https://www.phoenixcontact.com/us/products/2770891>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)