



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2017 (174) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with tin/lead solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #485893-9
011 HOUSING FFC PIN 100CL SR




TE Part #2362760-2
IDC PLUG, PBT



TE Part #1-2329383-2
PB OFF/ON FC RED M3 TERM. IP68



TE Part #2221760-1
AMPLIMITE IP67, SZ1, 90, 15 POS, RCPT



TE Part #CAT-R21-731
Heat Shrink Boots: Non Lipped, Straight



TE Part #1-5221128-7
PLUG,COMMERCIAL BNC



TE Part #2221612-1
Circ. HD Plug with pin contacts, 10 pos.



TE Part #2157468-1
PANEL MT RCPT,CIRCULAR HD,4 POS,S/C PINS



TE Part #2101676-2
RCPT,7 POS,Sz103 w/SOLDER CUPS, 240 POL

Documents

Product Drawings

PLUG,CIRCULAR HD,4 POS,w/SKT SLDR CUP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2157469-1_D_c-2157469-1-d.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2157469-1_D_c-2157469-1-d.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2157469-1_D_c-2157469-1-d.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English