



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **1**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Dimensions

Product Length	24.4 mm[.96 in]
----------------	-----------------

Packaging Features

Packaging Quantity	7500
--------------------	------

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight



Contact Mating Retention	Without
--------------------------	---------

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2238173-3
250 FASTON,REC.,22-12 AWG,TPBR

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(134)

Quick Disconnects(425)

Splices(4)


Customers Also Bought

TE Part #926933-3
WIRE PIN 18-17 AWG .01 PTPB

TE Part #1-111446-6
16 UNIV I/O, NO EARS,LEAD FREE

TE Part #2267074-2
PMS9P1B05M6RE


TE Part #1-1437719-3
T01-0540-S03-FEMALE PLUG CONNECTOR-CRIMP



TE Part #5069794007
CGPT-1.2/0.6-0-SP



TE Part #1624213-2
23SE 10KB 6.35X50FL B7 CAT




TE Part #350189-1
.058 DIA RECPT PC R/A LP 26-22



TE Part #7-2150131-7
OCEAN_2.0_SPARE_PART_KIT-090F140F



TE Part #1-240642-1
PLATE-FRONT SHEAR



TE Part #2267473-3
SIZE 23 PERIPHERAL SEAL, CPC

Documents

Product Drawings

250 FASTON HSG.,REC.,1 POS,BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-336369-5_E_c-3-336369-5-e.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-336369-5_E_c-3-336369-5-e.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-336369-5_E_c-3-336369-5-e.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

6,35 FASTON RECPTACLES AND TAB SLEEVES

English

Product Specification

English

Agency Approvals

UL Report

English



UL Report

English