



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 16

Connector Product Type: Housing

Operating Voltage: 600 VDC

Connector System: Wire-to-Wire

Sealable: Yes

Features

Packaging Features

Packaging Quantity	20
Packaging Method	Package

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Thread Size	1-3/8 - 18 UNEF-2A
Polarization Code	A
Panel Mount Feature Type	Flange
Mating Alignment Type	Keyed
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	Without

Housing Features

Body Orientation	Straight
Housing Color	Black



Housing Material	Nylon (UV Resistant)
Circular Connector Shell Size	23

Product Type Features

Connector Seal & Plug Type	Wire Entry Seal
Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	16
Number of Power Positions	4
Number of Signal Positions	12

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Socket
Contact Protection	With

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	Immersion

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1977891-1
SLD CPC RCPT ASSY,23-16,STD SX,
UV RESIS




TE Part # 1977890-1
SLD CPC RCPT ASSY,23-16,STD SX,
UV RESIS


Also in the Series | AMP CPC



Circular Connector Backshells &
Clamps(1)




Circular Power Connectors(423)




Connector Contacts(6)



Connector Hardware(12)



Power Contacts(6)




Sealing Sleeves(2)

Customers Also Bought



TE Part #1-917809-3
DYNAMIC D-5 TAB HSG D/R 6P X-X



TE Part #CAT-D9934-A83
Contact: Component To Wire ; 20-
45A , 20-8 wire size




TE Part #5750913-7
68 50SR CABLE CONN KIT



TE Part #5749195-2
68 50SR KIT,ST,UK



TE Part #181270-3
MOD 2 BUCHSE



TE Part #213841-4
PWRBAND PIN CNT ASSY,8-10,L.P.



TE Part #213847-3
POWERBAND CONT ASSY,SILVER PLT



TE Part #1-1478763-5
METAL BACKSHELL 15 WAY 45 DE



Documents

Product Drawings

SLD CPC PLUG ASSY,23-16,STD SX, UV RESIS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1977892-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1977892-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1977892-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English