

HC-STA-D25-HLFS-1STP16-ELC-AL - Housing



1424378

<https://www.phoenixcontact.com/us/products/1424378>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing D25, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x Pg16, height: 56 mm, cable gland: none, Standard

Commercial data

Item number	1424378
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APE
Catalog page	Page 529 (C-2-2019)
GTIN	4055626371184
Weight per piece (including packing)	115.5 g
Weight per piece (excluding packing)	114.1 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-D25-HLFS-1STP16-ELC-AL - Housing



1424378

<https://www.phoenixcontact.com/us/products/1424378>

Technical data


Notes

General	For contact inserts HC-D25, A16
---------	---------------------------------

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Product family	HC-STA-D
Application	Standard
Type	D25
No. of cable outlets	1
Type of the screw connection	1x Pg16
Type	Low design
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	30 mm
Height	56 mm
Length	80 mm

Material specifications

Seal material	NBR, conductive
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Type of the screw connection	1x Pg16
Locking type	Pin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-D25-HLFS-1STP16-ELC-AL - Housing


1424378

<https://www.phoenixcontact.com/us/products/1424378>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-D25-HLFS-1STP16-ELC-AL - Housing



1424378

<https://www.phoenixcontact.com/us/products/1424378>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424378>

DNV
Approval ID: TAE000037S

cUL Recognized
Approval ID: E255026

UL Recognized
Approval ID: E255026

cULus Recognized

HC-STA-D25-HLFS-1STP16-ELC-AL - Housing

1424378

<https://www.phoenixcontact.com/us/products/1424378>



Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-STA-D25-HLFS-1STP16-ELC-AL - Housing



1424378

<https://www.phoenixcontact.com/us/products/1424378>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com