




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2202165-5
QSFP TO QSFP, 26AWG, FDR, 5.0 METER



TE Part # 2202165-4
QSFP TO QSFP, 26AWG, FDR, 4.0 METER



TE Part # 1888810-2
EMI/Dust Cover, XFP And QSFP



TE Part # 2053453-5
C/A, QSFP TO 4XSFP+, 4.0M



TE Part # CAT-C11-H5011142
QSFP to QSFP I/O Cable Assembly: 33 AWG



TE Part # 1-2053638-6
C/A, QSFP, 0.5M, P1-P2, UNEQUALIZED



TE Part # CAT-C11-H50111
QSFP-Four SFP+ I/O Cable Assembly 30 AWG



TE Part # 2110819-1
QSFP+ Enh EVERCLEAR PT Conn


Also in the Series | **QSFP/QSFP+**




Light Pipes(8)



Pluggable I/O Cable Assemblies(13)



Pluggable IO Connectors & Cages(154)



QSFP, QSFP+ & zQSFP+(154)

Customers Also Bought




TE Part #6609021-5
3VB1=F7124 S0



TE Part #1735446-6
2MM PITCH HPI POST HEADER, VERTICAL, 6P



TE Part #5-6609929-0
PE0S0DH60=C2264



TE Part #53240-2
PG SP SPD 22-16COMM22-18MIL 6



TE Part #1934346-1
Tin Man Header Assy 3x16 Double



TE Part #1934332-1
Tin man Header Assy 5x16 Double



TE Part #2-6609129-8
SEFM4S=F8112



TE Part #1-1546406-1
ETHERNET CLOSURE CAP RECPT W /LANYRD



TE Part #2057760-2
[IMP100S,H,V3P8C,UG,OEW46,4.9](#)



TE Part #5-2227790-1
[IMP100,S,H,V3P8C,LG,OEW46,SL](#)

Documents

Product Drawings

[EMI Gasket, QSFP/XFP 1x1](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2132186-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2132186-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2132186-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.