



Product Compliance

For compliance documentation, visit the product page on TE.com>











EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Melamine (2.49% in Component Part) 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one (3.91% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # 1-2327679-8 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 1-2327679-6 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 3-2327679-0 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 2327679-1 RECEPTACLE ASSY, 56 POS, VERT, GEN Z
 TE Part # 1-2327679-1 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 2327679-3 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 2327679-7 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 2327679-9 RECEPTACLE ASSY, 56 POS, VERT, GEN Z
 TE Part # 2327679-8 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 1-2327679-7 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 1-2327679-3 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 1-2327679-4 RECEPTACLE ASSY, 56 POS, VERT, GEN Z
 TE Part # 1-2327679-5 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 1-2327679-9 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 2-2327679-0 Receptacle Assy, 56 Pos,Vert,Gen Z	 TE Part # 2327679-6 RECEPTACLE ASSY, 56 POS, VERT, GEN Z
 TE Part # 2327679-5 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 2327679-2 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	 TE Part # 2327679-4 RECEPTACLE ASSY, 56 POS, VERT, GEN Z	


Customers Also Bought




TE Part #6600383-5
MBXL VERT HDR 2P+16S+2P STR




TE Part #2-2129710-5
LEFT SIDE LGA3647-0 SOCKET-P0 FOR ODM




TE Part #1551920-7
ZQSFP+ CONNECTOR ASSEMBLY




TE Part #2333799-8
RCPT ASSY, VERT, 168 POS, SLIVER 2.0




TE Part #3-2360229-6
Low Profile Slimline SAS 16X V/T REC




TE Part #2333799-7
RCPT ASSY, VERT, 168 POS, SLIVER 2.0




TE Part #2345275-1
Module, female guide whisper C/A Module



TE Part #2375584-4
sliver 168P INTERPOSER TO SLIVER 4C+



TE Part #9-440054-1
2.0 MM PITCH HPI VERTICAL POST HEADERS



TE Part #3-2199154-8
DDR4 DIMM 288 Pin TH type