





LOC		DIST		REVISIONS					
DF		DO		F	LTR	DESCRIPTION	DATE	OWN	APVD
					C	REV PER 063D-0284-00	11-00	CT	RG

- 1
- 2
- 3
- 4
- 5
- MARKED WITH .047 [1.19] HIGH CHARACTERS. FAR SIDE REFERS TO WIDE SIDE OF KEYSTONE, NEAR SIDE REFERS TO NARROW SIDE OF KEYSTONE.
- STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS.
- THIS PLUG WILL MATE WITH ANY RECEPTACLE CONNECTOR WITH THE SAME INSERT ARRANGEMENT.
- MAXIMUM WIRE INSULATION USED WITH THIS CONNECTOR IS .054 [1.37] DIAMETER WITH GROMMET
- CONTACTS ARE PACKAGED SEPARATELY AND SHIPPED WITH CONNECTOR.



1218534-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 9/23/99	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS (INCHES (mm))		CHK CHAD BAKER 10-5-99		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHAD BAKER 10-5-99	NAME PLUG ASSY, SIZE 5, 78 POSN., SERIES 90, AMPLIMITE	
0 PLC ±.005 (0.13) 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±.		PRODUCT SPEC	SIZE A100779	
MATERIAL SEE CALLOUTS		APPLICATION SPEC	CAGE CODE 1218534	
FINISH SEE CALLOUTS		WEIGHT	RESTRICTED TO	
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	