

RLP73K2BR12JTD

✓ ACTIVE

CGS | CGS RLP73

TE Internal #: 2-2176056-7

Surface Mount Current Sensing Resistor, Thick Film, 1206, .5 W, .12 ohm, 5 %, ±200 ppm/°C, Solder, 2 Terminations, Height .55 mm [.022 in], CGS RLP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Current Sensing Resistor**

Element Type: **Thick Film**

Package Size Code: **1206**

Power Rating: **.5 W**

Resistance Value: **.12 Ω**

[All Thick Film Resistor: Current Sense \(142\)](#)

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Thick Film
Package Size Code	1206

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.5 W
Resistance Value	.12 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.1 mm[.122 in]



Product Width	1.55 mm[.061 in]
---------------	------------------

Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RLP73K2BR12JTD

Surface Mount Current Sensing Resistor, Thick Film, 1206, .5 W, .12 ohm, 5 %, ±200 ppm/°C, Solder, 2 Terminations, Height .55 mm [.022 in], CGS RLP73






TE Part # CAT-C339-R529A
Thick Film Resistor: Current Sense



TE Part # 2176050-8
RLP73N 1E R10 5% 5K RL

Also in the Series | CGS RLP73



Surface Mount Resistors(337)

Customers Also Bought



TE Part #1375820-7
CST-100 II HOUSING 7 POS




TE Part #5103309-2
A/L LOW PRO HDR 14P VERT BLACK



TE Part #207359-1
RECEPT HSG,3 POSN,METRIC



TE Part #207377-1
HSG,PLUG 6 POSN,METRIMATE



TE Part #2-216791-0
AMP LATCH D/P ASSY




TE Part #34111
SOLIS R 22-16 COMM 22-18 MIL 8




TE Part #1445336-1
LOOSE PC CONTACT TIN PLATED



TE Part #66601-9
III+ SKT,18-14,TIN,LP



TE Part #1-216093-6
AMP-LATCH PRE-ASSY DIL WITHO



TE Part #1-215911-6
16 WAY GREY MK II RECP



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2176056-7_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2176056-7_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2176056-7_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English