




Switches > Push Button Switches



Push Button Switch Product Type: **Anti-Vandal Switch**
Configuration (Pole-Throw): **Single Pole - Double Throw**
Number of Actuators: **Single**
Actuator Profile: **Flush**
Bushing Style: **Threaded**

Features

Industry Standards

IP Rating	IP67
-----------	------

Dimensions

	19 in
--	-------

Body Features

Case Material	PBT
Product Orientation	Vertical
Actuator Force	255 g[9 oz]
Actuator Profile	Flush
Bushing Style	Threaded

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	With
Actuator Style	Round Actuator



Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Push-On/Push-Off

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage Range	250 VAC

Contact Features

Switch Contact Plating Material	Silver
---------------------------------	--------

Housing Features

Process Sealed	Yes
----------------	-----

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>











EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1-2213766-0 AV19 SPM 0.4VA POWER LED YELLOW 12V	 TE Part # 1-2213767-8 AV19 SPM 0.4VA MOVE RING LED BLUE 12V	 TE Part # 1-2213766-2 AV19 SPM 0.4VA POWER LED YELLOW 24V	 TE Part # 1-2213766-8 AV19 SPM 0.4VA POWER LED BLUE 12V
 TE Part # 1-2213764-0 AV19 SPM 0.4VA FIX RING LED YELLOW 12V	 TE Part # 1-2316366-1 AV19 SPL 3A POWER LOGO R&Y 12V	 TE Part # 1-2317404-2 AV19 SPL 3A FIXED RING R&Y 24V	 TE Part # 1-2316531-6 AV19 DPM 3A MOVING RING R&B 24V
 TE Part # 1-2316366-3 AV19 DPM 3A POWER LOGO R&G 12V	 TE Part # 1-2317404-8 AV19 DPM 3A FIXED RING R&Y 24V	 TE Part # 1-2316542-7 AV19 DPM 3A SPOT LOGO R&Y 12V	 TE Part # 2342835-7 AVC19M FLAT AIO RGB RL 500MM /1X6




TE Part # 3-2213765-2
AV19 SPL 0.4VA SPOT LED YELLOW 24V



TE Part # 3-2213764-1
AV19 SPL 3A FIX RING LED YELLOW 24V




TE Part # 3-2317404-4
AV19 SPM 3A FIXED RING R&Y 12V FL




TE Part # 3-2316531-4
AV19 SPM 3A MOVING RING R&Y 12V FL



TE Part # 3-2316542-9
AV19 SPL 3A SPOT LOGO R&B 24V FL



TE Part # 3-2213764-2
AV19 SPL 0.4VA FIX RING LED YELLOW 24V



TE Part # 3-2213765-1
AV19 SPL 3A SPOT LED YELLOW 24V



TE Part # 3-2316542-3
AV19 SPM 3A SPOT LOGO R&B 24V FL

Also in the Series | Alcoswitch AV19



Anti-Vandal Switches(472)



Push Button Switches(472)

Customers Also Bought



TE Part #CAT-C73765-M1G
M12 Panel Mount Solder Cups



TE Part #1757836-3
AMPLIMITE,R/A RCPT ASY,109,ZN,3



TE Part #9-1879352-6
RR02 5% 3K0 AMMO




TE Part #T4112011021-000
M12 F, 2P GOLD A_CODE RA SHIELDED PG7



TE Part #T4112511051-000
M12 F, 5P GOLD D_CODE RA SHIELDED PG7



TE Part #81117-000
LS509-51 Liquid Level Sensor



TE Part #8-146250-6
72 MODII HDR DRST B/A .100CL



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2213766-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2213766-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2213766-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch

English

Agency Approvals

UL Report

English