




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECR-23-169188	16MAR2023	MV	JP
	E1	REVISED PER ECR-23-175978	26MAY2023	MV	JP
	F	REVISED PER ECR-23-182036	08AUG2023	AK	JP
	F1	REVISED PER ECR-23-188860	09OCT2023	AK	JP

- 1 MATERIAL:
HOUSING- THERMOPLASTIC, UL94V-0, BLACK
CONTACT- COPPER ALLOY
CAVITY CARRIER TAPE- BLACK CONDUCTIVE PLOYCARBONATE
- 2 FINISH:
CONTACT - TIN PLATE FOR -2,-3,2--3,2--2,
GOLD PLATE FOR 1--2,1--3.1--4,
- 3 POSTS SOLDERTAILS MUST COMPLY WITH TE SOLDERABILITY SPEC 109-11-12.
- 4 HEADER ARE SUPPLIED ON A 330.2mm DIAMETER REEL WITH 225 PARTS PER REEL. THE CAVITY CARRIER TAPE HOLDS 1 PART PER POCCKET, ORIENTED AS SHOW.

- 5 PRIMARY REELING DIRECTION
- 6 REVERSE-REELING DIRECTION

6	972366-3	1706504-2	147117-5	2	3-647166-2	2-2232980-2
6	972366-4	1706504-4	147117-5	4	3-647167-4	1-2232980-4
6	972366-3	1706504-3	147117-5	3	3-647166-3	2-2232980-3
5	972366-3	1706504-3	147117-5	3	3-647167-3	1-2232980-3
5	972366-3	1706504-2	147117-5	2	3-647167-2	1-2232980-2
5	972366-3	1706504-3	147117-5	3	3-647166-3	2232980-3
5	972366-3	1706504-2	147117-5	2	3-647166-2	2232980-2
DIRECTION OF REELING	COVER TAPE	CARRIER TAPE	PICK AND PLACE CAP	NO. OF POSITIONS	HEADER ASSEMBLY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN P.0	30JUN2015	 TE Connectivity								
			CHK D.7	30JUN2015									
			APVD D.7	30JUN2015									
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	NAME MTA100 HDR ASSY SURFACE MOUNT, FRICTION LOCK, .025 SQUARE STRAIGHT POST								
		0 PLC ±-		108-1050									
		1 PLC ±-		APPLICATION SPEC									
		2 PLC ±0.20		114-1019									
		3 PLC ±-		WEIGHT									
4 PLC ±-		ANGLES ±1°		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO					
MATERIAL		FINISH		A200779		C=2232980		-					
				CUSTOMER DRAWING				SCALE	11:1	SHEET	1 OF 2	REV	F1

D

D

C

C

B



B

A


A

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



CAP FOR HEADER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.Q	30JUN2015		TE Connectivity		
		CHK D.Z	30JUN2015				
		APVD D.Z	30JUN2015				
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ±-		MTA-100 HDR ASSEMBLY, SURFACE MOUNT,			
		1 PLC ±-		FRICTION LOCK, .025 SQUARE			
		2 PLC ±0.40(.015)		STRAIGHT POST			
		3 PLC ±-					
		4 PLC ±-					
MATERIAL		ANGLES FINISH ±1°		PRODUCT SPEC		SIZE	
				108-1050		CAGE CODE	
				APPLICATION SPEC		DRAWING NO	
				114-1019		RESTRICTED TO	
				WEIGHT		A200779C=2232980	
				-		-	
CUSTOMER DRAWING				SCALE		SHEET	
				4:1		2 OF 2	
						REV F 1	