




Switches > Push Button Switches



Push Button Switch Product Type: **Anti-Vandal Switch**
Configuration (Pole-Throw): **Double Pole - Double Throw**
Number of Actuators: **Single**
Actuator Profile: **Flush**
Bushing Style: **Threaded**

Features

Industry Standards

IP Rating	IP67
-----------	------

Dimensions

	22 in
--	-------

Body Features

Case Material	PBT
Product Orientation	Vertical
Actuator Force	357 g[12.6 oz]
Actuator Profile	Flush
Bushing Style	Threaded

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	With
Actuator Style	Round Actuator

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single



Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Push-On/Push-Off

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage Range	250 VAC

Contact Features

Switch Contact Plating Material	Silver
---------------------------------	--------

Housing Features

Process Sealed	Yes
----------------	-----

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2213772-5
AV22 SPM 3A MOVE RING LED RED 12V

TE Part # 1-2213772-3
AV22 SPM 3A MOVE RING LED GREEN 12V

TE Part # 1-2213772-7
AV22 SPM 3A MOVE RING LED BLUE 12V

TE Part # 2213771-1
AV22 SPM 3A NO LED

TE Part # 5-2213772-5
AV22 DPM 3A MOVE RING LED GREEN 24V





Also in the Series | Alcoswitch AV22

Anti-Vandal Switches(124)

Push Button Switches(124)

Customers Also Bought



 TE Part #640903-1 RECEPT,PIDG FASTON 22-18 250	 TE Part #640309-3 UMNL PIN 12-10 PTPPHBZ	 TE Part #34070 PG BUTT SPLC 22-16COMM22-18MIL	 TE Part #ADP-NM-NF-R-W N Plug to N Jack RA
 TE Part #2-36153-4 TERMINAL,PIDG R IR 20 10	 TE Part #5950112012 TFE-10-X-STK	 TE Part #926868-3 UNIV-MNL PIN 1	 TE Part #925387-2 110 FASTON HSG. REC. 1P CLEAR
 TE Part #AAB5759-00 95H1-25-18-1-B-CC-AD	 TE Part #YDTS26W2544420PN08 PLUG ASSY. HIGH PWR		

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-2213772-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-2213772-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-2213772-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch

English

Agency Approvals



[UL Report](#)

English