

626437-4

✓ ACTIVE

ELECTRO-TAP

TE Internal #: 626437-4

Tap Splice, 20 – 18 AWG, .5 – .8 mm² Wire, Red, Length 17.5 mm [.

688 in], Box, Stranded Wire, Discrete Wire, Fully Insulated,

ELECTRO-TAP

[View on TE.com >](#)

Terminals & Splices > Splices

Splice Type: **Tap Splice**Wire Size: **.5 – .8 mm²**Sealable: **No**Compatible Insulation Diameter Range: **4 mm [.157 in]****Features****Housing Features**

Housing Material	Nylon 6/6
------------------	-----------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Contact Features

Terminal Plating Thickness	2.54 – 5.08 µm[100 – 200 µin]
----------------------------	-------------------------------

Terminal Plating Material	Tin
---------------------------	-----

Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Box
------------------	-----

Dimensions

Tap Wire Size	.5 – .8 mm ²
---------------	-------------------------

Wire Size	.5 – .8 mm ²
-----------	-------------------------

Compatible Insulation Diameter Range	4 mm [.157 in]
--------------------------------------	----------------

Product Length	17.5 mm [.688 in]
----------------	-------------------

Product Type Features

Splice Type	Tap Splice
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Primary Product Color	Red
-----------------------	-----

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: DEC 2010 (44) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 626437-1
ELECTRO TAP ASSY

Also in the Series | [ELECTRO-TAP](#)

Splices(13)

Customers Also Bought



TE Part #182926-1
CPC PLUG ASSY SIZE 23-37



TE Part #3-640599-4
04P MTA156 CONN ASSY 18AWG
ORA



TE Part #444020-1
9P HSG ASS'Y JR/STD




TE Part #880310-1
2 WAY FF 250 HOUSING TAB NYLON
6.6 NAT



TE Part #880192-2
5 WAY FF 110 HSG REC NYLON 66
NATURAL



TE Part #626328-2
FF 250 RECEPTACLE 4.0-6.0 MM2
TPBR



TE Part #152302-5
2 WAY COMBO CONN. NAT.



TE Part #1-180984-0
FASTON 250 FLAG BOOT NYLON
NAT



TE Part #1-163081-2
.062 PIN ASSY 3+



TE Part #2310345-1
114017-ZZ

Documents

Product Drawings

ELECTRO TAP ASSY

English

CAD Files

Customer View Model

[ENG_CVM_626437-4_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_626437-4_E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_626437-4_E.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ELECTRO-TAP CABLE CONNECTOR/SPICE

English