




- 1 END "A" MATES WITH ALL BNC SERIES PLUGS
- 2 END "B" MATES WITH ALL 50 SERIES SCREW TYPE PLUGS
- 3 CONNECTOR MATERIAL AND FINISHES:
SHELLS: BRASS, SILVER PLATED
CONTACTS: BERYLLIUM COPPER, GOLD PLATED
INSULATORS: DIELECTRIC, KEL-F
WASHER: BRASS, SILVER PLATED
GASKET: SILICONE RUBBER, BLACK
SOLDER: Sn63Pb37
- 4 RAW MATERIAL CERTIFICATIONS REQUIRED FOR BOTH KEL-F INSULATORS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	.010
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	1°

FINISH

343

DWN
C SCHOLL

30 JAN 12

CHK
—

APVD
M STORRY

30 JAN 12

PRODUCT SPEC

APPLICATION SPEC

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

NAME
ADAPTER, BNC RECEPTACLE
TO S-50 RECEPTACLE
MDC P/N 053-0752-0001

SIZE
A2

CAGE CODE
98278

DRAWING NO
9-1532004-7

RESTRICTED TO
—

SCALE
8:1

SHEET
1 of 1

REV
B