



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series | Mini-Universal MATE-N-LOK

Connector Caps & Covers(2)	Connector Contacts(89)	Connector Seals & Cavity Plugs(17)	Connector Strain Relief(2)
Insertion & Extraction Tools(1)	PCB Headers & Receptacles(93)	Power Contacts(89)	Wire-to-Board Headers & Receptacles (93)

Customers Also Bought

TE Part #T4111402021-000 M12,MALE,STRAIGHT,B CODE,2P,PG9,GOLD	TE Part #532431-1 HDI RECP ASSY 3 ROW 75 POS	TE Part #532431-8 HDI RECP ASSY 3 ROW 165 POS	TE Part #9-1879129-2 RN 0402 2K49 0.1% 10PPM 1K RL
TE Part #4-1617108-0 PRMSC-26X = PRMS COTS SENSITIV	TE Part #4-794637-0 10P MICRO MNL ASSY,VRT,SMT LF	TE Part #1663069-1 OSP/BMA PCB JACK W/.195" LEGS	TE Part #2157023-2 A600,Sz1,Receptacle Assy,60/60/5Q2
TE Part #770966-1 02P MINI UMNL R/A HDR ASSY SN	TE Part #3-1393659-4 V42254B1202Q640=PC612 MESSERLE		



Documents

Product Drawings

06P MINI UMNL R/A HDR ASSY AU

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_770969-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_770969-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_770969-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

Agency Approval Document

English