




Connectors > Lighting Connectors > Plug & Socket Lighting Connector Accessories



Lighting Connector Accessory Type: Ring Clip

Connector System: Wire-to-Wire

Number of Positions: 2

Sealable: No

Connector & Contact Terminates To: Wire & Cable

Features

Body Features

Primary Product Color	Black
-----------------------	-------

Packaging Features

Packaging Method	Box
------------------	-----

Operation/Application

Circuit Application	Power
---------------------	-------

Product Type Features

Lighting Connector Accessory Type	Ring Clip
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
---------------------	---

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | NECTOR S



[Insertion & Extraction Tools\(3\)](#)



[Plug & Socket Lighting Connector Accessories\(42\)](#)



[Plug & Socket Lighting Connectors\(30\)](#)

Customers Also Bought




[TE Part #5749195-2](#)  
[68 50SR KIT,ST,UK](#)



[TE Part #293284-1](#)  
[NECTOR S BUS BAR BOOT](#)



[TE Part #1969442-5](#)  
[EP 2.5 TPA Housing, 5 Pos](#)



[TE Part #925856-2](#)  
[WIRE PIN 15.5-13.5 AWG .01 BR](#)



[TE Part #1571076-9](#)  
[PRASA1-16F-BB000=POWER ROCKER](#)



[TE Part #917804-3](#)  
[DYNAMIC D-5 TAB CONT. S L/P](#)



[TE Part #1969442-2](#)  
[EP 2.5 TPA Housing, 2 Pos](#)



[TE Part #1622252-1](#)  
[LR0204 1% 51K](#)



[TE Part #293387-2](#)  
[NECTOR S OUTLET HV-4 WHITE](#)



[TE Part #1740317-1](#)  
[NECTOR S DISTRIBUTOR ASSY 6 POS WHITE](#)

Documents

Product Drawings

[NECTOR S RING CLIP BLACK](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1740261-2\\_H.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_1740261-2\\_H.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1740261-2\\_H.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR\\_S\\_LINE\\_CONNECTOR\\_BROCHURE](#)

English

Product Specifications

[Application Specification](#)

English