



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2176308-7
RP 1E 0.1W 249K 0.1% 25PPM 5K RL

TE Part # 2176093-5
RP 2A 0.25W 10K 0.1% 25PPM 1K RL

TE Part # 4-2176306-8
RP 1E 0.1W 3K57 0.1% 25PPM 5K RL

TE Part # 1-2176092-8
RP 2A 0.25W 1K0 0.1% 25PPM 1K RL

TE Part # 2176308-5
RP 1E 0.1W 147K 0.1% 25PPM 5K RL

TE Part # 1625867-2
RP 1J 0.166W 10K 0.1% 25PPM 1K RL

Also in the Series | **Holsworthy RP73**

Surface Mount Resistors(4227)

Customers Also Bought

TE Part #9-1393211-4
T92S11D22-24

TE Part #5103310-2
A/L LOW PRO HDR 14P RA BLACK

TE Part #2-1879338-7
CPF 0603 49K9 1% 50PPM 1K RL

TE Part #8-2176307-8
RP 1E 0.1W 100K 0.1% 25PPM 5K RL

TE Part #9-2176305-4
RP 1E 0.1W 1K0 0.1% 25PPM 5K RL

TE Part #214782-E
EPSVA KS GDM4 EE 10 3,8 SN *
STROMVERSOR

TE Part #2176554-8
3430 A2 1% 1R8 150ppm 1k RL

TE Part #3-2176554-5
3430 A2 1% 24R 100ppm 1k RL



TE Part #1-2176554-0
3430 A2 1% 2R2 150ppm 1k RL



TE Part #2317171-1
AMPL REC, HD22, VERT, 15P, THREADED

Documents

Product Drawings

RP 1E 0.1W 1K37 0.1% 25PPM 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176306-8_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2176306-8_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2176306-8_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RP73-0915

English