

HC-STA-B48-HHFS-1STM32-EM-AL - Housing



1424860

<https://www.phoenixcontact.com/us/products/1424860>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B48, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x M32, height: 107.5 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1424860
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 645 (C-2-2019)
GTIN	4055626382654
Weight per piece (including packing)	598 g
Weight per piece (excluding packing)	590 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B48-HHFS-1STM32-EM-AL - Housing



1424860

<https://www.phoenixcontact.com/us/products/1424860>

Technical data


Notes

General	This housing can be combined with cable glands with a maximum wrench size of 58 mm
---------	--

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B48
No. of cable outlets	1
Type of the screw connection	1x M32
Type	Tall design
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	90 mm
Height	107.5 mm
Length	132 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Type of the screw connection	1x M32
Locking type	Pin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)

HC-STA-B48-HHFS-1STM32-EM-AL - Housing

1424860

<https://www.phoenixcontact.com/us/products/1424860>



Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B48-HHFS-1STM32-EM-AL - Housing


1424860

<https://www.phoenixcontact.com/us/products/1424860>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B48-HHFS-1STM32-EM-AL - Housing



1424860

<https://www.phoenixcontact.com/us/products/1424860>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424860>

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026

cULus Recognized

HC-STA-B48-HHFS-1STM32-EM-AL - Housing



1424860

<https://www.phoenixcontact.com/us/products/1424860>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-STA-B48-HHFS-1STM32-EM-AL - Housing



1424860

<https://www.phoenixcontact.com/us/products/1424860>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com