







Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

K 776280 H - XX - PT X
① ② ③ ④ ⑤ ⑥

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Row No.Pin No:XX-08 Pin
- 5.Material:PT-PBT
- 6.Color:X:B-Black ; W-White ; GY-Gray ; BL-Blue



K776280H-XX-PTX	PBT	K776280W	K776280T
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal




DSND	SCALE: N/A	MODEL TYPE: 4.0mm Automobile connector
DWN	VIEW:	PART NO.: K776280H-XX-PTX
CHKD	UNIT: mm/in	DWG NO.: X-K776280H-XX-PTX
APPD	SIZE: A4	

Δx	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED





WEIGHT	SHEET	REVISION
	1/1	A0



Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

K 776280 H - XX - PT X
① ② ③ ④ ⑤ ⑥

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Row No.Pin No:XX-14 Pin
- 5.Material:PT-PBT
- 6.Color:X:B-Black ; W-White ;
GY-Gray ; BL-Blue



K776280H-XX-PTX	PBT	K776280W	K776280T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5




REVISIONS

UNSPECIFIED TOLERANCES




XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 4.0mm Automobile connector
DWN		VIEW:	PART NO.: K776280H-XX-PTX
CHKD		UNIT: mm/in	DWG NO.: X-K776280H-XX-PTX
APPD		SIZE: A4	
		WEIGHT	SHEET
			1/1
		REVISION	A0



Temperature range:-40℃-+125℃
温度范围：-40℃-+125℃



K 776280 H - XX - PT X
① ② ③ ④ ⑤ ⑥


- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Row No.Pin No:XX-23 Pin
- 5.Material:PT-PBT
- 6.Color:X:B-Black ; W-White ;
GY-Gray ; BL-Blue

K776280H-XX-PTX	PBT	K776280W	K776280T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						






DSND		SCALE: N/A	MODEL TYPE: 4.0mm Automobile connector
DWN		VIEW:	PART NO.: K776280H-XX-PTX
CHKD		UNIT: mm/in	DWG NO.: X-K776280H-XX-PTX
APPD		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT	SHEET
			REVISION
		1/1	A0



Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

K 776280 H - XX - PT X
 (1) (2) (3) (4) (5) (6)

- 1.K: XKBTEK-Car Connector
2.XKB Series No
3.Category:H-Housing
4.Row No.Pin No:XX-35 Pin
5.Material:PT-PBT
6.Color:X:B-Black ; W-White ;
GY-Gray ; BL-Blue



K776280H-XX-PTX	PBT	K776280W	K776280T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal


DSND		SCALE: N/A	MODEL TYPE: 4.0mm Automobile connector		
DWN		VIEW: 	PART NO.: K776280H-XX-PTX		
CHKD		UNIT: mm/in	DWG NO.: X-K776280H-XX-PTX		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxb.com www.helloxb.cn www.xk-dg.cn						


XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED



槽位说明




颜色：黑色



颜色：灰色



颜色：本色



颜色：蓝色