










PART NO.
20449-001E
20449-001E-01



Mating

Notes

- Material
 - Housing : LCP (GF=30%) black UL94-V-0
 - Contact : brass
Au 0.05 μm MIN. over Ni 1.27 μm MIN.
 - Ground contact : phosphor bronze
Au 0.03 μm MIN. OVER Ni 1.27 μm MIN.
- Coplanarity : 0.1mm MAX
- Packing : emboss tape
- Mating partner part No.
20448-001R-081, 20462-001E
- This is "Pb-free" connector
- RoHS compliant

Notes

- 材料
 - ハウジング: LCP (GF=30%) 黒 UL94-V-0
 - コンタクト: 黄銅
Au 0.05 μm MIN. over Ni 1.27 μm MIN.
 - グランドコンタクト: リン青銅
Au 0.03 μm MIN. OVER Ni 1.27 μm MIN.
- コプラナリティ: 0.1mm MAX
- 梱包: エンボステープ
- 嵌合相手 part No.
20448-001R-081, 20462-001E
- 本コネクタは"Pb-free"である
- RoHS指令を満足している

GENERAL TOLERANCE	
6 MAX.	±0.2
6 OVER MAX. 30	±0.3
30 OVER MAX. 120	±0.5
ANGLE	±2°

5	Z12144	S.M	Mar./22/12	Tom	DESIGN'D BY	DATE
4	Z11644	H.M	Dec./06/'11	E.K	K.Ohbayashi	Nov/12/'07
3	Z10351	H.M	Aug/17/'10	E.K	CHK'D BY	DATE
2	Z10351	H.M	Aug/02/'10	E.K		
1	Z08315	K.O	Jul/08/'08	E.K	APP'D BY	DATE/UNIT
REV	ECN	BY	DATE	APP	E.Kawabe	Nov/13/'07
REV.RECORD					CUSTOMER COPY	PROJECTION
SERIES No.					R3	SCALE
					UNIT	DWG. No.
					20:1	mm
					20449	



TITLE		MHF4 Connector receptacle		General	
SHEET	REV.	1/1	5		