

HC-B-TA-M40-PLR-BK - Adapter



1414246

<https://www.phoenixcontact.com/us/products/1414246>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic thread adapter with bayonet lock, for EVO housing series B, M40 thread



Commercial data

Item number	1414246
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	BF7APL
Catalog page	Page 659 (C-2-2019)
GTIN	4055626021997
Weight per piece (including packing)	42.2 g
Weight per piece (excluding packing)	32.6 g
Customs tariff number	85389099
Country of origin	PL

HC-B-TA-M40-PLR-BK - Adapter



1414246

<https://www.phoenixcontact.com/us/products/1414246>

Technical data


Product properties

Product type	Thread adapter
Application	Bayonet B - metric
Type of the screw connection	M40

Connection data

Tightening torque	... 10 Nm
-------------------	-----------

Dimensions

Dimensional drawing	
Thread type on seal side	M40

Internal dimensions

Length of internal thread	12 mm
---------------------------	-------

Material specifications

Material	PA
Flammability rating according to UL 94	V0
Seal material O-ring	NBR
Housing material	PA

Mechanical properties

Mechanical data

Type of the screw connection	M40
------------------------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 80 °C

Mounting

Assembly note	Bayonet locking max. 3x can be removed The plastic thread adapter does not establish an electrical connection between the cable gland and connector housing. For this reason, only plastic cable protection systems or plastic cable glands may be used.
---------------	---

HC-B-TA-M40-PLR-BK - Adapter


1414246

<https://www.phoenixcontact.com/us/products/1414246>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-TA-M40-PLR-BK - Adapter



1414246

<https://www.phoenixcontact.com/us/products/1414246>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414246>

**DNV**
Approval ID: TAE000037S

**cUL Recognized**
Approval ID: E255026

**UL Recognized**
Approval ID: E255026

**EAC**
Approval ID: RU C-DE.AI30.B.01102

cULus Recognized

HC-B-TA-M40-PLR-BK - Adapter

1414246

<https://www.phoenixcontact.com/us/products/1414246>



Classifications

ECLASS

ECLASS-11.0	27144432
ECLASS-12.0	27140801
ECLASS-13.0	27140801

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-B-TA-M40-PLR-BK - Adapter

1414246

<https://www.phoenixcontact.com/us/products/1414246>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	1.674 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com