



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense

Resistor Type: **Low Ohmic Resistor**Element Type: **Thick Film**Package Size Code: **0805**Power Rating: **.25 W**Resistance Value: **.062 Ω** [All Thick Film Resistor: Current Sense \(190\)](#)

Features

Product Type Features

Resistor Type	Low Ohmic Resistor
Element Type	Thick Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.25 W
Resistance Value	.062 Ω
Resistance Class	Up to 1k Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm [.022 in]
Product Length	2 mm [.079 in]

Product Width	1.25 mm [.049 in]
---------------	-------------------

Usage Conditions

Temperature Coefficient	± 400 ppm/ $^{\circ}$ C
-------------------------	-----------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://te.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}$ C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C339-R529A
Thick Film Resistor: Current SenseTE Part # 2176050-8
RLP73N 1E R10 5% 5K RL

Also in the Series | CGS RLP73



Surface Mount Resistors(337)

Customers Also Bought

TE Part #5747301-8
37 RCPT SP/FMS INSRTTE Part #CAT-104MTA-PVUNH
PCB Header: Polyester, Vertical,
Unshrouded, No Mating AlignmentTE Part #292317-4
STD USB TYPE B, R/A, T/HTE Part #1825140-2
MGDH04STR04=1/2 PITCH LOW P
DIP T&RTE Part #1-2324271-3
RIGHT SEGMENT LGA4189-4
SOCKET P4 FOR ODMTE Part #1-2324271-4
LEFT SEGMENT LGA4189-4 SOCKET-
P4 FOR ODMTE Part #1-2340321-2
ASSY STRADDLE MOUNT 168P 076
SLIVER 2.0TE Part #2336568-3
RECEPT ASSY, RA, 168 POS, SLIVER
2.0TE Part #2345506-2
RECEPTACLE ASSY, WITH END
WALL, POWER

Documents

Product Drawings

RLP73M 2A R062 1% 1K RL

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2176053-3_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176053-3_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176053-3_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English