



#### General Information

Series	KHA
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No

#### Dimensions

D	12.5mm MAX
T	4.5mm MAX
S	7.5mm NOM
F	0.6mm +/-0.1mm

#### Packaging Specifications

Packaging	T&R, 360mm, H0 = 16mm, Component Pitch = 25.4mm
Packaging Quantity	500

#### Specifications

Capacitance	1500 pF
Capacitance Tolerance	10%
Voltage DC	2000 VDC
Dielectric Withstanding Voltage	4000 VDC
Temperature Range	-55/+125°C
Temperature Coefficient	X7R