





NORES:

- 1. Rated voltage: 600V AC.DC
- 2. Rated current: 50A AC DC (MAX)
- 3. Contact resistance: $\leq 20 \text{ m}\Omega$
- 4. Insulation resistance: $\geq 1000 \text{ m}\Omega$
- 5. Withstand voltage: 2200V AC/minute
- 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- 7. Materials: LCP UL94V-0, Color: Black
- 8. Matched RoHS criteria

REV.	REVISION DESCRIPTION	DATE	APPD

Circuits	Product name	Dimension mm			
		A	B	C	D
2	DL5200B-2AWS	10.00	20.90	1.80	3.50
2	DL5200B-2AWS-D	10.00	20.90	2.60	5.10
2	DL5200B-2AWS-Z	10.00	20.90	3.40	5.10
2	DL5200B-2AWS-G	10.00	20.90	6.58	8.30
3	DL5200B-3AWS	20.00	30.90	1.80	3.50
3	DL5200B-3AWS-D	20.00	30.90	2.60	5.10
3	DL5200B-3AWS-Z	20.00	30.90	3.40	5.10
3	DL5200B-3AWS-G	20.00	30.90	6.58	8.30
4	DL5200B-4AWS	30.00	40.90	1.80	3.50
4	DL5200B-4AWS-D	30.00	40.90	2.60	5.10
4	DL5200B-4AWS-Z	30.00	40.90	3.40	5.10
4	DL5200B-4AWS-G	30.00	40.90	6.58	8.30
5	DL5200B-5AWS	40.00	50.90	1.80	3.50
5	DL5200B-5AWS-D	40.00	50.90	2.60	5.10
5	DL5200B-5AWS-Z	40.00	50.90	3.40	5.10
5	DL5200B-5AWS-G	40.00	50.90	6.58	8.30
6	DL5200B-6AWS	50.00	60.90	1.80	3.50
6	DL5200B-6AWS-D	50.00	60.90	2.60	5.10
6	DL5200B-6AWS-Z	50.00	60.90	3.40	5.10
6	DL5200B-6AWS-G	50.00	60.90	6.58	8.30

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL1X002 (DL5200B)-AWS		TITLE: 10.00 mm pitch WTB Connector Wafer	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 24.01.10	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 24.01.10	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 24.01.10	UNITS: mm	REV.: A
DRAWING NO:					



REV.	REVISION DESCRIPTION	DATE	APPD.

NOTES

Used in DL1X002-Y Series Housing.

Accepts AWG #12~8 Wire Range.

Material : Copper Alloy

Finish: Gold plated or Tin plated.

Thickness: 0.5 mm.

Matched RoHS criteria

Product name	Dimension mm				适配线规
	A1	B1	A2	B2	AWG
DL5200B-T	6.1	6.6	5.4	6.2	#12-10
DL5200B-T-G	6.0	5.5	5.9	7.5	#8

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	.X°: $\pm 3.0^\circ$	PRODUCT NAME: DL1X002 (DL5200B)-T		TITLE: 10.00 mm pitch Crimp Terminal	
.XX: ± 0.15	.X°: $\pm 2.0^\circ$	APPD: Chen Quan Long		DATE: 24.01.11	
.XXX: ± 0.01	.X°: $\pm 1.0^\circ$	CHKD: Wu Hui		DATE: 24.01.11	
DRAWING NO:		DR: Ren An De		SCALE: N/A	PAGE: 1/1
				UNIT: mm	REV.: A