



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 293647-1
NECTOR S OUTLET BRIDGE ASS'Y US


Customers Also Bought



TE Part #293224-5
NECTOR S PANEL OUTLET LV-2



TE Part #293235-4
NECTOR S T SPLITTER SERIAL LV2-LV2



TE Part #5433696013
CGPT-24/8-0-55MM



TE Part #NB10256001
ATUM-24/8-0-55MM




TE Part #1740315-1
NECTOR S COVER FOR
DISTRIBUTOR 6,7 POS



TE Part #1740335-1
MICRO QUADLOK SYSTEM PIN
CONTA



TE Part #1740317-1
NECTOR S DISTRIBUTOR ASSY 6 POS
WHITE



TE Part #1586075-4
4P RCPT VAL-U-LOK V2 BLK



TE Part #2151969-1
OCEAN_2.0_APPLICATOR-S-
055F062O-RSM



TE Part #293234-1
NECTOR S T SPLITTER

Documents

- CAD Files

Customer View Model

[ENG_CVM_293225-1_D.3d_igs.zip](#)

English
- Customer View Model

[ENG_CVM_293225-1_D.3d_stp.zip](#)

English
- Customer View Model

[ENG_CVM_293225-1_D.2d_dxf.zip](#)



English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_CVM_293225-1_D1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293225-1_D1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293225-1_D1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English