




Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors > AMPLIMITE D-Sub Receptacle Assembly: Vertical, 1.27mm



Connector & Housing Type: **Plug**
Connector System: **Cable-to-Board**
Number of Positions: **60**
Centerline (Pitch): **1.27 mm [.05 in]**
Number of Rows: **2**

[All AMPLIMITE D-Sub Receptacle Assembly: Vertical, 1.27mm \(41\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Rectangular Termination Post & Tail Width	.45 mm[.017 in]
Rectangular Termination Post & Tail Thickness	.4 mm[.015 in]
Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.1 mm[.122 in]

Packaging Features

Packaging Quantity	80
Packaging Method	Tray

Operation/Application

Shielded	No
Circuit Application	Signal



Mechanical Attachment

Mating Alignment	Without
PCB Mount Alignment	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Board Mount

Body Features

Primary Product Color	Black
Connector Profile	Standard

Contact Features

	30 μin
Contact Options	Installed
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin, Tin over Nickel
Contact Shape & Form	Square
Contact Current Rating (Max)	1 A

Dimensions

PCB Thickness (Recommended)	.8 – 1.6 mm
Row-to-Row Spacing	2.54 mm[.1 in]

Housing Features

Housing Material	PBT
Centerline (Pitch)	1.27 mm[.05 in]

Product Type Features

Shell Material Configuration	All Plastic
Connector & Housing Type	Plug
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	60
Number of Rows	2
PCB Mount Orientation	Vertical



Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 5174215-5
AMPLIMITE.050 PLUG ASS'Y (V) 20P
PB-FREE



TE Part # CAT-020-DPAV127
D-Sub Plug Assembly: Standard,
Vertical, 1.27mm


Also in the Series | **AMPLIMITE 0.50 Series**



Connector Caps & Covers(20)



Connector Hardware(7)



D-Sub Backshells & Clamps(31)



IDC D-Sub Connectors(62)



PCB D-Sub Connectors(172)

Customers Also Bought



TE Part #1586681-2
12P UMNL PIN HDR ASSY 94VO omit
#2



TE Part #6-1879510-7
CRGH0805 1% 5K62 0.33W




TE Part #9-1879514-5
CRGH1206 1% 1K02 0.5W



TE Part #4-1624121-4
3621E 220UH 10%



TE Part #2298196-2
MTA-100 HEADER ASSEMBLY



TE Part #3734873001
55A0121-12-2/6



TE Part #1586681-8
12P UMNL PIN HDR ASSY 94VO omit
#8



TE Part #1586682-3
09P UMNL HDR ASSY PC 94VO SL
#8



Documents

Product Drawings

AMPLIMITE.050 PLUG ASS'Y (V) 60P PB-FREE

English

CAD Files

Customer View Model

ENG_CVM_CVM_5174215-4_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5174215-4_O.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_5174215-4_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_5174215-4_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_5174215-4_A1.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_5174215-4_A1.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Specification

English

5174215-4

Plug, Cable-to-Board, 60 Position, 1.27 mm [.05 in] Centerline, 2 Row, Square, Standard Profile, Vertical, AMPLIMITE 0.50 Series, PCB D-Sub Connectors

