




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought





TE Part #4-1462037-7
IM07GR=IM RELAY 200mW 24VDC



TE Part #1-1393210-8
T9AS1D12-24



TE Part #215083-8
MICRO-MATCH MOW.08P




TE Part #350210-1
03P CMNL HDR ASSY PC NATL



TE Part #350782-1
09P UMNL CAP HSG



TE Part #1393219-6
PE014012



TE Part #723955-000
BPTM-30/12-A/U-4(S30)



TE Part #3-178141-5
DYNAMIC D3100 HDR V 6P ASSY



TE Part #7-1393222-2
V23061B1002A301=MINISTARKSTROM

TE Part #2-1437514-2
322-HCS5P2-102=HOLTITE REEL AS

Documents

Product Drawings
OUAZ-SS-124L,900

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1419131-1_E4.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1419131-1_E4.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1419131-1_E4.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



OUAZ series Relay data sheet English

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English