





1. MAXIMUM PANEL THICKNESS = 6.35 [.25]
2. USE HAND TOOL 220022-2.
3. USE INSTRUCTION SHEET 408-9821.



RECOMMENDED PANED CUTOUT
SCALE 4:1



RECOMMENDED STRIP LENGTH
SCALE 4:1

RG-59/U, 59A/U, 59B/U, 62/U, 62A/U, 62B/U		1-329631-2	1-329632-2	328633	9-50428-0	225057-2	225060-4	5225059-3
FOR USE WITH CABLE		⑥ JAM NUT QTY=1	⑤ LOCK WASHER QTY=1	④ GASKET QTY=1	③ FERRULE QTY=1	② CONTACT QTY=1	① JACK ASSEMBLY QTY=1	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES]  TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.41 [016] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -				DWN J. HAVENER 01MAR2005		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
				CHK J. HAVENER 01MAR2005				
				APVD J. LIPPERT 01MAR2005		NAME JACK, BULKHEAD, SHV		
				PRODUCT SPEC —		—		
				APPLICATION SPEC —		—		
MATERIAL —		WEIGHT —		SIZE A1		CAGE CODE 00779		DRAWING NO 5225059
CUSTOMER DRAWING		SCALE 8:1		SHEET 1 OF 1		REV 0		