




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5536507-4
2MM FB,ASY,192,SIG,REC,SL,2.73




TE Part # 5536510-4
2MM FB,ASY,192,SIG,REC,SL,3.53




TE Part # 5536511-4
2MM FB,ASY,192,SIG,REC,EN,3.55


Also in the Series | Z-PACK Future Bus+




Backplane Connector Housings(19)



Board-to-Board Headers & Receptacles(14)



Hard Metric Backplane Connectors(1)



PCB Headers & Receptacles(14)

Customers Also Bought



TE Part #5557969-1
MJ,TE,8P/8C,SHLD,PNL STOPS&G



TE Part #6-1879259-4
RP 2B 2K0 0.1% 15PPM CUT LENGT




TE Part #8-1625868-4
RP 2A 0.25W 39R2 0.1% 25PPM 1K RL




TE Part #1879259-1
RP 2B 1K21 0.1% 15PPM CUT LENGTH




TE Part #1-1879259-9
RP 2B 1K4 0.1% 15PPM CUT LENGTH



TE Part #ZPF000000000009493
992 IH 10SL 3 PN 1 A909




TE Part #ZPF000000000009496
992 IH 14S 5 PN 1



TE Part #ZPF000000000009609
992-02H 10SL 3 PN 1 A316



TE Part #ZPF000000000019061
FDBA 54H 14-19 PN-K



TE Part #ZPF00000000001830
164-8013-06



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5536501-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5536501-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5536501-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English