




LOC		DIST		REVISIONS					
ES	00	P	LTR	DESCRIPTION		DATE	DWN	APVD	
		C		ADDED NEW PN 1-8, 1-9		21JUN2023	DP	HW	
		C1		ADDED 2-1		16MAR2024	DP	HW	
		C2		NOTE 2 DELETED		09OCT2024	VNB	RCG	







- OPTIONAL CENTER MODULE.
- DELETED
- MATERIAL: THERMO PLASTIC, UL94 V-0.
- DATUM LOCATIONS AND BASIC DIMENSIONS TO BE ESTABLISHED BY THE CUSTOMER.
- BULKHEAD THICKNESS RANGE: .031 - .100
- CONNECTOR MATED TO PANEL FROM OPPOSITE SIDE.
- NO BURRS ALLOWED ON OPPOSITE (MATING) SIDE.
- CONNECTOR KEEP OUT ZONE.
- MOUNT CONNECTOR WITH TYCO HARDWARE KIT (1600914-7) FOR .050 [1.27mm] MIN RADIAL FLOAT.
- FOR THE CONFIGURATION WITH VENT, PLEASE REFER TO SHEET 2
- FOR VARIABLE DIMENSIONS, PLEASE SEE PART TABLE



IOP	1892901-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.ZHOU CHK S.ZHAO APVD S.ZHAO	27JUL2009 27JUL2009 -	TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		±" ±.01 ±.005 ±.0020 #2° -		PRODUCT SPEC 108-2175 APPLICATION SPEC 114-13112	
MATERIAL 3		WEIGHT -		SIZE A100779	
Customer Drawing		Customer Drawing		SCALE 4:1	
SHEET 1		OF 4		REV C2	

LOC		DIST		REVISIONS				
ES	00	P	LTR	DESCRIPTION		DATE	DWN	APVD
		-		SEE SHEET 1		-	-	-



FOR THE CONFIGURATION WITH VENT HOLES

2.800	1.890	.375	.370	2.240	3.290	5ACP	2-1892901-1
3.400	2.490	.300	.370	2.840	3.890	8ACP(8AWG)	1-1892901-9
2.200	1.290	.300	.370	1.640	2.690	4ACP(8AWG)	1-1892901-8
2.550	1.640	.400	.395	1.990	3.040	4P(10AWG)	1-1892901-7
5.200	4.290	.300	.370	4.640	5.690	14ACP(8AWG)	1-1892901-6
5.200	4.290	.300	.370	4.640	5.690	14ACP(8AWG)	1-1892901-5
2.150	1.240	.300	.345	1.590	2.640	4ACP(8AWG)	1-1892901-1
2.700	1.790	.350	.370	2.140	3.190	5ACP(8AWG)	1-1892901-0
2.890	1.980	.115	.3025	2.330	3.380	16LP(14AWG)	1892901-9
3.650	2.740		.345	3.090	4.140	11P	1892901-8
2.950	2.040	.425	.345	2.390	3.440	5P	1892901-7
1.850	.940	.300	.345	1.290	2.340	3ACP	1892901-6
3.550	2.640	.375	.370	2.990	4.040	7ACP	1892901-5
2.375	1.465	.375	.345	1.815	2.865	4P	1892901-4
1.850	.940	.300	.345	1.290	2.340	3ACP	1892901-3
3.000	2.090	.250	.345	2.440	3.490	8P	1892901-2
3.000	2.090	.200	.320	2.440	3.490	10P	1892901-1
DIM H	DIM D	DIM S	DIM K	DIM L	DIM F	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0 PLC ±.01
1 PLC ±.01
2 PLC ±.01
3 PLC ±.005
4 PLC ±.0020
ANGLES ±.2°
FINISH

MATERIAL

DWN
C. ZHOU
CHK
S. ZHAO
APVD
S. ZHAO

27JUL2009
27JUL2009
-

PRODUCT SPEC
108-2175
APPLICATION SPEC
114-13112
WEIGHT

Customer Drawing

NAME
PANEL MOUNT CABLE RECEPTACLE HOUSING WITH SLIM GUIDES MULTI-BEAM XLE

SIZE
A1

CAGE CODE
100779

DRAWING NO
1892901

RESTRICTED TO
-

SCALE
4:1

SHEET
2


OF
4

REV
C2

TE Connectivity

PART NUMBER	ROWS		POWER					
			P5	P4	P3	P2	P1	
1892901-7	D C B A							
5P								




PART NUMBER	ROWS	POWER		
		P3	P2	P1
1892901-6	D C B A			
3 ACP				




09				TE Connectivity	
NAME					
PANEL MOUNT CABLE RECEPTACLE HOUSING WITH SLIM GUIDES MULTI-BEAM XLE					
SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
A1	00779	C-1892901		-	
		SCALE	4:1	SHEET 3 OF 4	REV C2

4805 (3/11)


LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




NO CONTACTS LOADED




5ACP




4ACP




4P




4ACP




NO CONTACTS LOADED



NO CONTACTS LOADED



8ACP



5ACP

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.ZHOU

27JUL2009

DIMENSIONS:
INCHES

0 PLC ±"
1 PLC ±.01
2 PLC ±.01
3 PLC ±.005
4 PLC ±.0020
ANGLES ±2°
FINISH -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

DWN
S.ZHAO

27JUL2009

PRODUCT SPEC
108-2175
APPLICATION SPEC
114-13112

DWN
S.ZHAO

27JUL2009

MATERIAL
-

DWN
S.ZHAO

27JUL2009

Customer Drawing

DWN
S.ZHAO

27JUL2009

TE Connectivity

PANEL MOUNT CABLE RECEPTACLE HOUSING WITH SLIM GUIDES MULTI-BEAM XLE

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=1892901

RESTRICTED TO
-

SCALE
4:1

SHEET
4

OF
4

REV
C2