



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0805**

Power Rating: **.1 W**

Resistance Value: **1.5K Ω**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.1 W
Resistance Value	1.5K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]



Product Width	1.25 mm[.049 in]
---------------	------------------

Usage Conditions

Temperature Coefficient	±25 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


CPF-A-0805B1K5E1

Surface Mount Precision Resistor, Thin Film, 0805, .1 W, 1.5K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Height .55 mm [.022 in], Neohm CPF





TE Part # 5-2176217-6
CPF A 0805 25K 0.1% 25PPM 1K RL



TE Part # 2-2176237-5
CPF A 0603 680R 0.1% 25PPM 5K RL



TE Part # 4-2176217-9
CPF A 0805 10K 0.1% 25PPM 1K RL



TE Part # 6-2176216-5
CPF A 0603 200K 0.1% 25PPM 1K RL




TE Part # 4-2176215-5
CPF A 0402 68K 0.1% 25PPM 1K RL

Also in the Series | Neohm CPF




Surface Mount Resistors(5842)

Customers Also Bought



TE Part #281698-8
HEADER HE14 RA 8 P



TE Part #5177983-3
0.8FH,R05H.5,080,08/Sn,TU



TE Part #1676250-1
RN 0805 20K 0.1% 10PPM CUT LENGTH



TE Part #6-534206-3
26 MODII VRT DR CE 100/115




TE Part #9-146276-0
40 MODII HDR SRST B/A .100CL



TE Part #3-2176217-4
CPF A 0805 1K2 0.1% 25PPM 1K RL



TE Part #1-1625959-5
HB03RE 20M 1% 100PPM



TE Part #1-929504-5
2X 7P JUN-POW-TIMGH

CPF-A-0805B1K5E1

Surface Mount Precision Resistor, Thin Film, 0805, .1 W, 1.5K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Height .55 mm [.022 in], Neohm CPF



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2176217-5_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2176217-5_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2176217-5_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Automotive Grade Thin Film Chip Resistor - Type CPF-A Series

English