

# HC-B-TA-PG21-PLR-BK - Adapter

1414249

<https://www.phoenixcontact.com/us/products/1414249>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic thread adapter with bayonet lock, for EVO housing series B, Pg21 thread



## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1414249             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | BF57                |
| Product key                          | BF7APL              |
| Catalog page                         | Page 659 (C-2-2019) |
| GTIN                                 | 4055626022123       |
| Weight per piece (including packing) | 22.5 g              |
| Weight per piece (excluding packing) | 21.8 g              |
| Customs tariff number                | 85389099            |
| Country of origin                    | PL                  |

# HC-B-TA-PG21-PLR-BK - Adapter

1414249

<https://www.phoenixcontact.com/us/products/1414249>



## Technical data

### Product properties

|                              |                |
|------------------------------|----------------|
| Product type                 | Thread adapter |
| Application                  | Bayonet B - Pg |
| Type of the screw connection | Pg21           |

### Connection data

|                   |          |
|-------------------|----------|
| Tightening torque | ... 8 Nm |
|-------------------|----------|

### Dimensions

|                          |      |
|--------------------------|------|
| Dimensional drawing      |      |
| Thread type on seal side | Pg21 |

### Internal dimensions

|                           |       |
|---------------------------|-------|
| Length of internal thread | 11 mm |
|---------------------------|-------|

### Material specifications

|  |     |
|--|-----|
| Flammability rating according to UL 94 | V0  |
| Seal material O-ring                   | NBR |
| Housing material                       | PA  |

### Mechanical properties

|                              |      |
|------------------------------|------|
| Mechanical data              |      |
| Type of the screw connection | Pg21 |

### Environmental and real-life conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient conditions              |                   |
| Degree of protection            | IP66              |
| Ambient temperature (operation) | -40 °C ... 100 °C |

### Mounting

|               |   |
|---------------|---|
| Assembly note | Bayonet locking max. 3x can be removed<br><br>The plastic thread adapter does not establish an electrical connection between the cable gland and connector housing. For this reason, only plastic cable protection systems or plastic cable glands may be used. |
|---------------|---|

# HC-B-TA-PG21-PLR-BK - Adapter


1414249

<https://www.phoenixcontact.com/us/products/1414249>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-B-TA-PG21-PLR-BK - Adapter

1414249

<https://www.phoenixcontact.com/us/products/1414249>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414249>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026



**EAC**

Approval ID: RU C-DE.AI30.B.01102

**cULus Recognized**

# HC-B-TA-PG21-PLR-BK - Adapter

1414249

<https://www.phoenixcontact.com/us/products/1414249>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27144432 |
| ECLASS-12.0 | 27140801 |
| ECLASS-13.0 | 27140801 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000441 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# HC-B-TA-PG21-PLR-BK - Adapter

1414249

<https://www.phoenixcontact.com/us/products/1414249>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.273 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)