

## Main

Product Range	Harmony Electromechanical Relays
Product Type	Socket
Product Compatibility	Relay 792XDX Relay 782XDXH Relay 792XBX Diode 70-BSMD Signalling device 70-BSMLG Suppressor module 70-BSMM
Number of Terminals	14
Switch Function	4PDT
Contact Composition	4 C/O

## Complementary

Rated Current	10 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Panel screw clamp terminals, clamping connection capacity:2 x 2.5...2 x 4 mm <sup>2</sup> , AWG 14...AWG 12 solid for output Panel screw clamp terminals, clamping connection capacity:2 x 2.5...2 x 4 mm <sup>2</sup> , AWG 14...AWG 12 stranded for output
Tightening Torque	Chassis 0.8 N.m, AWG 14...AWG 12, copper Screw 0.8 N.m
Fixing Mode	By screw, M3 panel Clip-on 35 mm symmetrical DIN rail
Shape of Screw Head	Combination roundhead
Product Weight	2.2 oz (62 g)
Width	1.2 in (30 mm)
Depth	3.11 in (79.06 mm)

## Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...158 °F (-40...70 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL[RETURN]CSA[RETURN]CE

## Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480278099
Returnability	No
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.31 in (8.4 cm)
Package 1 Width	1.18 in (3 cm)
Package 1 Length	1.57 in (4 cm)
Package 1 Weight	2.2 oz (62 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.80 in (7.1 cm)
Package 2 Width	3.31 in (8.4 cm)
Package 2 Length	5.98 in (15.2 cm)
Package 2 Weight	21.9 oz (621 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	6.69 in (17 cm)
Package 3 Width	12.60 in (32 cm)
Package 3 Length	17.32 in (44 cm)
Package 3 Weight	27.43 lb(US) (12.44 kg)

## Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No
Carbon footprint (kg CO2 eq, Total Life cycle)	1