

Han 10B Protect Cover with pin Thermopla



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 010 5407
Specification	Han 10B Protect Cover with pin Thermopla
HARTING eCatalogue	https://b2b.harting.com/09300105407

Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings Thermoplastic

Version

Size	10 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
	4
Type rating acc. to UL 50 / UL 50E	4X 12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140045293
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors