

RLP73N2AR18FTDF

✓ ACTIVE

CGS | CGS RLP73

TE Internal #: 1-2176053-4

Surface Mount Low Ohmic Resistor, Thick Film, 0805, .25 W, .18 ohm, 1 %, ±300 ppm/°C, Solder, 2 Terminations, Height .55 mm [.022 in], CGS RLP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Low Ohmic Resistor**

Element Type: **Thick Film**

Package Size Code: **0805**

Power Rating: **.25 W**

Resistance Value: **.18 Ω**

[All Thick Film Resistor: Current Sense \(190\)](#)

Features

Product Type Features

Resistor Type	Low Ohmic Resistor
Element Type	Thick Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.25 W
Resistance Value	.18 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]



Product Width	1.25 mm[.049 in]
---------------	------------------

Usage Conditions

Temperature Coefficient	±300 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RLP73N2AR18FTDF

Surface Mount Low Ohmic Resistor, Thick Film, 0805, .25 W, .18 ohm, 1 %, ±300 ppm /°C, Solder, 2 Terminations, Height .55 mm [.022 in], CGS RLP73





TE Part # CAT-C339-R529A


[Thick Film Resistor: Current Sense](#)



TE Part # 2176050-8

[RLP73N 1E R10 5% 5K RL](#)

Also in the Series | [CGS RLP73](#)



[Surface Mount Resistors\(337\)](#)

Customers Also Bought




TE Part #640454-4

[04P MTA100 HDR ASSY SQ STR POL](#)




TE Part #3-640440-4

[04P MTA100 CONN ASSY 22AWG RED](#)



TE Part #215079-4

[MICRO-MATCH FOB.04P](#)



TE Part #2-521105-2

[ULTRA-FAST 187 ASY REC 22-18 TPBR](#)



TE Part #2329386-1

[PN OFF/ON FC BLK M1 TERM IP68 500MM LHS](#)

Documents

[Product Drawings](#)
[RLP73N 2A R18 1% 1K RL](#)

English

[CAD Files](#)
[3D PDF](#)

3D



Customer View Model

[ENG_CVM_CVM_1-2176053-4_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176053-4_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176053-4_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD Low Ohmic Current Sense Resistors - Type RL73 Series](#)

English