

# HC-STA-D50-HHFD-1STP21-EL-AL - Housing

1424406

<https://www.phoenixcontact.com/us/products/1424406>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing D50, for double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x Pg21, height: 80 mm, cable gland: Pg21, Standard

## Commercial data

Item number	1424406
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APE
Catalog page	Page 532 (C-2-2019)
GTIN	4055626371467
Weight per piece (including packing)	253.1 g
Weight per piece (excluding packing)	253.1 g
Customs tariff number	85389099
Country of origin	CN

# HC-STA-D50-HHFD-1STP21-EL-AL - Housing

1424406

<https://www.phoenixcontact.com/us/products/1424406>



## Technical data

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Product family	HC-STA-D
Application	Standard
Type	D50
No. of cable outlets	1
Type of the screw connection	1x Pg21
Type	Tall design
Cable outlet	lateral
Pg screw connection	Pg21

### Dimensions

Dimensional drawing	
Width	56 mm
Height	80 mm
Length	82 mm

### Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

### Mechanical properties

Mechanical data	
Type of the screw connection	1x Pg21
Locking type	Pin

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-STA-D50-HHFD-1STP21-EL-AL - Housing


1424406

<https://www.phoenixcontact.com/us/products/1424406>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-STA-D50-HHFD-1STP21-EL-AL - Housing

1424406

<https://www.phoenixcontact.com/us/products/1424406>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424406>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026

**cULus Recognized**

## Classifications

### ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

### ETIM

ETIM 9.0	EC000437
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-STA-D50-HHFD-1STP21-EL-AL - Housing

1424406

<https://www.phoenixcontact.com/us/products/1424406>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	5.402 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)