



All D-Sub Crimp Recpt Signal 25 Posn, Socket Size 20, Shell Size 3 (9)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #2176230-8
3522 3R3 5% 3W




TE Part #5-1879233-9
SMW5 27R 5%




TE Part #206438-1
CPC RECPT ASSEMBLY SIZE 23-57



TE Part #5146800-1
BATT INT,KEYLESS,5P,7.2V




TE Part #5787253-1
MDI REC ASS'Y ,6P



TE Part #2842123-3
3P,2MM,BRK HDR,SRRT,2.8,0.38AU, BOX



TE Part #GAG15K4D489
ESAP-ESA PROBE-400601408



TE Part #5787253-2
MDI REC ASS'Y ,6P



TE Part #1-644751-0
10P MTA156 HDR ASSY R/A



TE Part #1337708-2
0.5MM CSA BRAID M3 -M3 150MM

Documents

Product Drawings

25 HD20 RCPT ASSY (CN)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_207516-6_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_207516-6_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_207516-6_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English