

Switches > Push Button Switches

Push Button Switch Product Type: **Anti-Vandal Switch**Configuration (Pole-Throw): **Single Pole - Single Throw**Number of Actuators: **Single**Actuator Profile: **Flush**Bushing Style: **Threaded**

Features

Industry Standards

IP Rating	IP67
-----------	------

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver

Body Features

Case Material	PBT
Product Orientation	Vertical
Actuator Force	255 g[9 oz]
Actuator Profile	Flush
Bushing Style	Threaded

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	With
Actuator Style	Round Actuator

Configuration Features

Configuration (Pole-Throw)	Single Pole - Single Throw
----------------------------	----------------------------

Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Momentary

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage Range	250 VAC

Housing Features

Process Sealed	Yes
----------------	-----

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2213763-7
AV19 DPL 3A NO LED



TE Part # 3-2213766-7
AV19 SPL 3A POWER LED BLUE 12V



TE Part # 2213763-5
AV19 DPM 3A NO LED




TE Part # 2213767-3
AV19 SPM 3A MOVE RING LED
WHITE 24V




TE Part # 2213763-1
AV19 SPM 3A NO LED

Also in the Series | [Alcoswitch AV19](#)



Anti-Vandal Switches(472)



Push Button Switches(472)

Customers Also Bought



TE Part #2387549-3
CU ALLOY,INNER FERRULE,120SQ



TE Part #172130-1
FF 250 REC HSG 2P NYLON NAT



TE Part #170335-1
PL 250 RECEPTACLE 15-10 AWG
PTPBR



TE Part #170340-1
FF 250 TAB 20-14AWG BR
WITHOUT
LATCH



TE Part #170031-1
FF 250 REC 20-14AWG BR



TE Part #170384-1
250 FASTON,REC.,22-20 AWG,BR



TE Part #170032-2
250 FASTON,REC.,20-14 AWG,BR



TE Part #2-2213766-5
AV19 SPL 3A POWER LED RED 12V



TE Part #L9000082-01
Antenna Dipole 2.4GHz Tilt Swivel
SMA



TE Part #1717109-1
0.64 III 16POS PLUG ASSY

Documents

Product Drawings

AV19 SPM 3A SPOT LOGO R&B 12V

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2316542-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2316542-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2316542-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch

English

Agency Approvals

UL Report

English