



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 175048-1
FF 187 TAB 2-3MM2 PTBR

TE Part # 281197-5
FF 187 REC 1.0-2.5MM2 PTBR (RE REELING)

TE Part # 281197-6
FF 187 REC 1.0-2.5MM2 PTBR

TE Part # 281197-2
FF 187 REC 1.0-2.5MM2 PTBR

TE Part # 640841-1
BLADE REC 250 20-16AWG BR

TE Part # 175042-1
FF 187 REC 2-3MM2 PTBR

TE Part # 280098-2
FF 250 REC 1-2.5MM2 TPPB

TE Part # 5-160446-5
FF 250 REC 1.0-2.5MM2 TBBR

TE Part # 60434-1
FF 187 TAB 20-16AWG TPBR

TE Part # 280080-2
FF 250 TAB TERMINAL 11-10 AWG PTPB

TE Part # 280919-2
FF 187 REC 0.5-1.5MM2 TPBR

Also in the Series | FASTIN-FASTON 187

Crimp Terminal Housings(6)

Insertion & Extraction Tools(1)

Quick Disconnects(20)

Customers Also Bought

TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM, HOUSING

TE Part #1376109-1
025 TAB CONT

TE Part #353537-1
040-3 UNSEALED CONT.TAB(S)

TE Part #1827855-1
0.50 SERIES CONNECTER RECEPTACLE CONTACT



Documents

Product Drawings

FF 187 REC 0.5-1.25MM2 PTBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_175040-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_175040-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_175040-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

APPLICATION SPECIFICATION CRIMPING .187 SERIES TAB AND RECEPTCLE CONTACTS

Japanese

Application Specification

Japanese

APPLICATION SPECIFICATION CRIMPING .187 SERIES TAB AND RECEPTCLE CONTACTS

English