



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 3

Connector Product Type: **Housing**

Operating Voltage: **250 VDC**

Connector System: **Wire-to-Wire**

Sealable: **Yes**

Features

Dimensions

Compatible Insulation Diameter Range	2.41 – 5.21 mm[.095 – .205 in]
--------------------------------------	--------------------------------

Packaging Features

Packaging Quantity	24
Packaging Method	Package

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Thread Size	15/16-20 UNEF – 2A
Polarization Code	A
Panel Mount Feature Type	Flange with Mounting Holes
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With



Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Nylon
Circular Connector Shell Size	17

Product Type Features

Connector Seal & Plug Type	Peripheral, Wire Entry Seal
Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	With
Number of Positions	3
Number of Power Positions	3
Number of Signal Positions	0

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	Yes
Contact Type	Socket
Contact Protection	With

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	Immersion

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------



Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2423641-1
SEAL CAP ASSY, SZ17, SR 5&6,
PLASTIC LAN




TE Part # 4-2407269-4
CAP, CPC, SIZE 17 RECP, YELLOW



TE Part # 788188-2
CPC 17-3 PLUG ASY,REV SEX



TE Part # 4-2407269-3
CAP, CPC, SIZE 17 RECP, RED



TE Part # 4-2407269-1
CAP, CPC, SIZE 17 RECP, ORANGE



TE Part # 2423641-2
SEAL CAP ASSY, SZ17, SR 5&6, METAL BEAD



TE Part # 788188-1
CPC 17-3 PLUG ASY,REV SEX



TE Part # 4-2407269-2
CAP, CPC, SIZE 17 RECP, BLACK

Also in the Series | AMP CPC




Circular Connector Backshells & Clamps(1)



Circular Power Connectors(423)




Connector Contacts(6)



Connector Hardware(12)



Power Contacts(6)



Sealing Sleeves(2)

Customers Also Bought




TE Part #HDP24-24-19PN-L017
REC, 19P, BLK, N, RNG, 12/16, P




TE Part #CAT-AL4-SBD355002
Battery Disconnect, 500A, 2 Pole



TE Part #1-794069-0
18P MINI UMNL HDR W/DH SN LF



TE Part #807079-000
382A023-4/42-0



TE Part #321259
TERMINAL,SOLIS FLAG R 4/0 1/2



TE Part #4-1609134-8
20ESRM2=F8278



TE Part #CAT-AL8-STPBSC
Push Button Switch, Center Thread, 1 Actuator, Flush Profile



TE Part #K1153104
Safety Cap TS-2 06-63-170



Documents

Product Drawings

CPC 17-3 RCPT ASY,REV SEX

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_788189-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_788189-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_788189-1_B.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_788189-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_788189-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_788189-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications

Product Specification

English