







P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REVISED PER ECO-13-018116	20NOV2013	KH	JO
E		REVISED PER ECR-22-137476	23AUG2022	RK	SD
E1		REVISED PER ECN-23-224702	04AUG2023	RK	MF
E2		DRAFTING UPDATES	12SEP2024	AR	SP




- 1 GLASS FILLED THERMOPLASTIC, UL 94-V0 RATED, COLOR:BLACK
- 2 EJECTOR FEATURES AT MOLDER'S DISCRETION (QUANTITY AND LOCATION).
- 3 THE PRODUCT IS NOT YET QUALIFIED AND IS IN PROCESS.



REAR VIEW OF CONNECTOR



SCALE 3:1



SCALE 3:1

65.99	25	52	2-104482-0
55.83	21	44	1-104482-9
50.75	19	40	1-104482-8
48.21	18	38	1-104482-7
45.67	17	36	1-104482-6
43.13	16	34	1-104482-5
40.59	15	32	1-104482-4
38.05	14	30	1-104482-3
35.51	13	28	1-104482-2
32.97	12	26	1-104482-1
27.89	10	22	1-104482-0
25.35	9	20	104482-9
22.81	8	18	104482-8
20.27	7	16	104482-7
17.73	6	14	104482-6
15.19	5	12	104482-5
12.65	4	10	104482-4
10.11	3	8	104482-3
7.57	2	6	104482-2
5.03	1	4	104482-1
DIM "C"	NO OF SP	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: SCOTT A. SHUE 18MAY89	TE Connectivity	
DIMENSIONS: mm		CHK: H. MOLL 18MAY89		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: R. FLICKER 18MAY89	NAME: RCPT HSG, DBL ROW, 2.54x2.54 CL SHORT PT, AMPMODU	
0 PLC ±		PRODUCT SPEC		
1 PLC ±		APPLICATION SPEC	SIZE: 00779 C=104482	
2 PLC ±		WEIGHT		
3 PLC ±		CUSTOMER DRAWING	SCALE 8:1 SHEET 1 OF 1 REV E2	
4 PLC ±				
ANGLES FINISH				