



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #788154-2
SLD CPC RCPT ASSY,11-4,REV SEX



TE Part #2820893008
44A0111-28-9



TE Part #NB-PTCO-157
Pt1000, 2.0x2.3, Class B, PTFC102B1A0



TE Part #2820203012
44A0111-20-0





TE Part #282034-012
44A0111-22-4



TE Part #214347-E
SMCB 50 F AB VV 6-01 VH * 0008 137
E002



TE Part #214348-E
SMCB 68 F AB VV 6-01 VH * 0008 137
E002



TE Part #364198-E
SRCBUG A 2,54 2 2 CSI 112 E1 ADV
TRAY J



TE Part #374335-E
DRCBUG B 2,54 20 * CSI 112 E012
ADV J 2



TE Part #464771-E
SRCROL A 2,54 2 C1820 10TS 137 *
9999 J