

# Han B Protect Cover Die Cast for Hood PG



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 024 5426
Specification	Han B Protect Cover Die Cast for Hood PG
HARTING eCatalogue	<a href="https://b2b.harting.com/09300245426">https://b2b.harting.com/09300245426</a>

## Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> B
Type of accessory	Protection cover
Description of the accessory	for cable to cable housing
	Metal
	With fixing cord

## Version

Size	24 B
Locking type	Double locking lever

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance  
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	72 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140047983
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors