





TAPE AND REEL PACKAGING
PACKAGING UNIT; 100 PCS

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
G1		DRAWING RE-CREATED IN CREO	28DEC2023	NK	JDB
G2		PIN HEIGHT CORRECTION	19FEB2024	NK	JDB
G3		REEL CORE DIA ADDED	23JUL2024	KA	LET
G4		PIN 1 MARKING CORRECTION	16OCT2024	SS	LET



SECTION A-A



PCB-LAYOUT PROPOSAL



CODING

INSPECTION LEVEL 1: CONTROL CHART REQUIRED

① PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED

② PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3

1	-	TAPE AND REEL	6
1	-	PAD	5
1	-	SHIELD	4
1	-	CONNECTOR SHIELD	3
8	-	PINS	2
1	-	HOUSING	1
394811-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY		PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 12JUL2023		 TE Connectivity							
		CHK M SZELAG 15JUL2023									
		APVD J DE BRUIJN 15JUL2023									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK DIN 7167		NAME M12 FEMALE, X CODE, 8P, 17MM SMT/THR, CAT6A							
				PRODUCT SPEC 108-94886							
				APPLICATION SPEC 114-94781							
				WEIGHT -							
				CUSTOMER DRAWING							
MATERIAL - -		FINISH -		SIZE A3		CAGE CODE 00779		DRAWING NO C-394811-E		RESTRICTED TO -	
				SCALE 5:1		SHEET 1 OF 1		REV G4			

1. COPLANARITY OF ALL CONTACT ≤ 0.1 MM
2. MISSING INFORMATION AND DIMENSIONS PER DIN EN 61076-2-109